


FEATURES

- Multifunction- 10 different modes
- 17.5mm width
- DIN Rail mounting
- LED indications for power and relay status
- SPCO output relay
- 100ms-100hrs timing range
- IP20 (terminals), IP40 (enclosure) protection
- Wide voltage range Offers a "one stop solution" for your power management system
- The two LED status indicators indicate status at a glance

RS PRO SPDT Multi Function Timer Relay - 0.1 s \rightarrow 100 h, 1 Contacts, Multi Function, DIN Rail

RS Stock No.: 896-6813



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



Product Description

RS PRO multi-function time delay relay is made to a high degree of precision and accuracy. The time settings can be set easily by using the knob on the front of the time delay relay.

General Specifications

Switch Configuration	SPDT
Mode of Operation	Multi-Function
Contact Configuration	CO
Number of Timer Functions	10
Number of Contacts	1
Time Range	0.1s to 100h
Time Increment	Hours, Minutes, Seconds
Time Delay	200ms (Reset)
Power on indication / Timing	Green LED
Relay Status	Red LED
Applications	Production, Safety, On-delay timers, Off-delay timers, Interval-on-operate, Flasher, Repeat cycle

Electrical Specifications

Power Supply	External
Supply Voltage	12V to 240V ac/dc
Minimum Voltage	12VAC/DC
Maximum Voltage	240VAC/DC
Current Maximum	6A
Current Minimum	0.1A
Terminal Type	Screw

Timer Relays



Mechanical Specifications

Mounting Type	DIN-Rail
Depth	10mm
Width	100mm
Length	30mm
Minimum Panel Thickness	3.5mm
Weight	60g

Operation Environment Specifications

Maximum Operating Temperature	60°C
Minimum Operating Temperature	-10°C

Protection Category	
IP Rating	IP20; IP40

Approvals

Compliance/Certifications	CE, RoHS



Timer Relays



