


FEATURES

- 17.5mm width
- On/Off function
- DIN Rail mounting
- 100ms-100hrs timing range
- LED status indication for power and relay status
- SPCO output relay
- Wide supply voltage range
- IP20 (terminals), IP40 (enclosure) protection

RS PRO SPDT Multi Function Timer Relay - 0.1 s \rightarrow 100 h, 1 Contacts, Asymmetric OFF/ON, Asymmetric ON/OFF, DIN

RS Stock No.: 896-6826



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



Product Description

RS Asymmetrical Timer is dual function and multi-voltage for flexibility. It is compact in size and DIN Rail mountable

General Specifications

Switch Configuration	SPDT
Mode of Operation	Asymmetric OFF/ON, Asymmetric ON/OFF
Contact Configuration	СО
Number of Timer Functions	Multi-Function
Number of Contacts	1
Time Range	0.1s to 100h
Time Increment	Hours, Minutes, Seconds
Time Delay	200ms (Reset)
Reset Time	200ms
Applications	Production, Safety, On-delay timers, Off-delay timers, Interval-on-operate, Flasher, Repeat cycle

Electrical Specifications

Power Supply	External
Supply Voltage	12V to 240V ac/dc
Minimum Voltage	12V ac/dc
Maximum Voltage	240V ac/dc
Current Maximum	8A
Current Minimum	0.1A
Relay Output	SPCO
Terminal Type	Screw

Timer Relays



Mechanical Specifications

Mounting Type	DIN-Rail
Depth	65 mm
Width	18 mm
Length	85 mm

Operation Environment Specifications	
Maximum Operating Temperature	60°C
Minimum Operating Temperature	-10°C

Protection Category	
IP Rating	IP20; IP40

Approvals	
Compliance/Certifications	CE, RoHS



Timer Relays



