

## ENGLISH

#### Datasheet

# RS Pro 1 Channel Digital DIN Rail Time Switch Measures Hours, $110 \rightarrow 240$ V ac RS Stock No: 896-6888



#### **Product Details**

RS Pro time switch with 1 channel, supports 12/24 h display formats. This digital DIN rail has a supply voltage of 110 to 240 V ac. This astronomical switch is built-in a compact design and is ideal for outdoor and street lighting applications. The time switch features easy manual override and keypad lock.

#### **Features and Benefits**

- 35 mm wide
- 3 lines text LCD
- DIN rail mounting
- Latitude/longitude precise to the minute with time zone
- Sunrise/sunset or twilight rise/set trigger modes
- Easy programming and navigation
- DST, offset, Off hours, weekly Off features
- 12/24 hours display format
- 6 years battery reserve
- 110-240 V ac supply voltage

RS, Professionally Approved Products, gives you professional quality parts across all products categories. Our range has been testified by engineers as giving comparable quality to that of the leading brands without paying a premium price.



# ENGLISH

## Specifications:

Units Measured	Hours
Battery Life	6 yr
Depth	65 mm
Height	90 mm
Number of Channels	1
Contact Configuration	CO
Segment Length	1 min
Supply Voltage	110 to 240 V ac
Туре	Digital
IP Rating	IP20, IP40
Number of Operating Modes	3
Power Consumption	6 VA