

## Datasheet

# RS Pro Hours Run Meter, 6 digits, Digital, Spade Terminal Connection, 10 → 80 V dc

RS Stock No: **896-6936**



## Product Details

RS Pro hours run meter has a robust design that enables a high degree of accuracy and it has 36.8 x 24.1 mm cut-out size. The design of this rectangular meter makes it totally sealed from dust and moisture. It has 6 digit display with digital spade terminal connection and has a supply voltage of 10 to 80 V dc.

## Features and Benefits

- 7 different bezel style models
- Panel mount
- 6 digits non-resettable with automatic recycle to zero
- Compact and robust design provides shock and vibration protection
- Wide supply voltage range
- IP66 protection

**Specifications:**

Approvals	CE; cRUus; NEMA 4X; RoHS Compliant; SAE
Count Direction	Up
Function	Hour Meter
Meter Type	Electronic
Shape	Rectangular
Cutout Height	24.1 mm
Cutout Width	36.8 mm
Depth	70.95 mm
Maximum Count Frequency	50/60 Hz
Maximum Measurement	99999.9 h
Measurement Range	0 to 99999.9 h
Meter Accuracy	±0.02%
Minimum Measurement	0 h
Minimum Operating Temperature	-40°C
Number of Digits	6
Weight	47 g
Connection Type	Spade
Count Capacity	99999.9 h
Cutout Size	36.8 x 24.1 mm
Digit Height	3.6 mm
Display Type	Digital
Input Type	Voltage
Mounting Type	Panel Mount
Reset Method	No Reset
Supply Voltage	10 to 80 V dc
Humidity Rating	95%
IP Rating	IP65
Power Rating	0.25 VA