



Filter mat, Extract: W: 125 mm, H: 125 mm, IP54, Quality class G3

Model	
product brand name	SIVACON
product designation	filter mat
design of the product	Class G3
fan design / withdrawable fan	No
design of the product / EMC version	No
General technical data	
cutout width	125 mm
cutout height	125 mm
operating temperature / minimum	-10 °C
Protection class	
protection class IP	IP54
Product details	
product component / fan	No
Mechanical Design	
height	118 mm
width	118 mm
installation location	Control cabinet side panels, door, vertical
fastening method	snap-on mounting
fastening method	
• 19-inch installation	No
• wall mounting	Yes
net weight	0.05 kg
material	plastic
Certificates	
reference code	
• acc. to DIN EN 61346-2	V
• acc. to IEC 81346-2	V
General Product Approval	



Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mfb=8MR6000-0AM25>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8MR6000-0AM25>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mfb=8MR6000-0AM25

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

