Adjustable wrench with thin jaw



Product features

- Good accessibility, slim jaws 45% thinner than a standard wrench of same size
- Big opening, jaws open 40% wider than a standard adjustable wrench of same size
- Strong and durable, torque resistance exceeds ASME and ISO specifications
- Precision hardened and anti-corrosion treated
- Measurement scale in mm
- Conform to: ISO 6787, DIN 3117 Form A, angle 15°, UNE 16532, BS 6333, ASME B107.8M-2003







Product code	EAN-code	Packaging pcs	Dimensions mm	Weight g
9031-T	7314150131648	5	20x263x69	325