

Datasheet

Din Rail Mount Optocoupler, 6A DC, 100-240VAC

RS Stock number 905-4302



Specifications:

Rated input voltage	100-240V AC
Rated input current	8 mA
Status indicator	LED
Max. switching frequency	60 Hz
Rated switching voltage	3-30V DC
Rated switching current	6 A
Voltage Drop at Max	<1V
Operating Temperature	-25°C to 60°C
Storage Temperature	-40°C to 70°C
Rated impulse withstand voltage	2.5kW
Wire strip length	11mm
Insulating material	PA
Dimensions (HxWxD)	61.7 x 91 x 6.2mm