



ASUS DRW-24D5MT optical disc drive Internal DVD Super Multi DL Black

Brand : ASUS

Product code: 90DD01Y0-B20010

Product name : DRW-24D5MT



CD+/-RW, DVD+/-RW, DVD DL, 4-24 x, 145ms DVD, 125ms CD, 146 x 170 x 41 mm, 650g
 ASUS DRW-24D5MT. Product colour: Black, Mounting: Vertical/Horizontal. Purpose: Desktop, Optical drive
 type: DVD Super Multi DL, Interface: SATA. DVD+R write speed: 24x, CD-R write speed: 48x, CD-RW
 write speed: 24x. CD-R read speed: 48x, CD-RW read speed: 40x, CD-ROM read speed: 48x. DVD drive
 average random access time: 145 ms, CD-ROM drive average random access time: 125 ms

Design		Access Time	
Internal *	✓	DVD drive average random access time	145 ms
Product colour	Black	CD-ROM drive average random access time	125 ms
Mounting	Vertical/Horizontal		
Performance		Record Modes	
Purpose *	Desktop	Track-at-once (TAO)	✓
Optical drive type *	DVD Super Multi DL	Disc-at-once (DAO)	✓
Interface *	SATA	Session-at-once (SAO)	✓
Disc types supported	CD,CD-R,CD-ROM,CD-RW,DVD,DVD+R,DVD+R DL,DVD+RW,DVD+RW DL,DVD-R,DVD-R DL,DVD-ROM,DVD-RW	Packet writing	✓
Optical disc diameter	80,120 mm	Sequential writing	✓
		Random write	✓
Writing Speed		System Requirements	
CD-R write speed	48x		Windows 10 Education,Windows 10 Education x64,Windows 10 Enterprise,Windows 10 Enterprise x64,Windows 10 Home,Windows 10 Home x64,Windows 10 Pro,Windows 10 Pro x64,Windows 7 Enterprise,Windows 7 Enterprise x64,Windows 7 Home Basic,Windows 7 Home Basic x64,Windows 7 Home Premium,Windows 7 Home Premium x64,Windows 7 Professional,Windows 7 Professional x64,Windows 7 Starter,Windows 7 Starter x64,Windows 7 Ultimate,Windows 7 Ultimate x64,Windows 8,Windows 8 Enterprise,Windows 8 Enterprise x64,Windows 8 Pro,Windows 8 Pro x64,Windows Vista Business,Windows Vista Business x64,Windows Vista Enterprise,Windows Vista Enterprise x64,Windows Vista Home Basic,Windows Vista Home Basic x64,Windows Vista Home Premium,Windows Vista Home Premium x64,Windows Vista Ultimate,Windows Vista Ultimate x64,Windows XP Home x64,Windows XP Professional,Windows XP Professional x64
CD-RW write speed	24x	Windows operating systems supported	
DVD+R write speed *	24x		
DVD-R write speed	24x		
DVD-R Double Layer write speed	8x		
DVD+R Double Layer write speed	8x		
DVD+RW write speed	8x		
DVD-RW write speed	6x		
Reading Speed			
CD-R read speed	48x		
CD-RW read speed	40x		
CD-ROM read speed	48x		
DVD+R read speed	16x		
DVD-R read speed	16x		
DVD-RW read speed	8x		
DVD-RAM read speed	5x		
DVD-ROM read speed	16x		
DVD+R Double Layer read speed	12x		
DVD+RW read speed	13x		
		Operational Conditions	
		Operating relative humidity range	20 - 80%
		Operating temperature range (T-T)	5 - 45 °C
		Storage temperature range (T-T)	-20 - 60 °C
		Storage relative humidity range	15 - 90%

Weight & Dimensions

Width	146 mm
Depth	170 mm
Height	41 mm
Weight	650 g

Packaging Content

Bundled software	Cyberlink Power2Go 8 Cyberlink PowerBackup E-Green
------------------	--

Technical Details

Playback disc formats	CD audio, DVD-Video, Picture CD
-----------------------	---------------------------------



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.