

## Pneum. contact metal ID 6 female




Image is for illustration purposes only. Please refer to product description.

Part number	09 14 000 6406
Specification	Pneum. contact metal ID 6 female
HARTING eCatalogue	<a href="https://b2b.harting.com/09140006406">https://b2b.harting.com/09140006406</a>

### Identification

Category	Contacts
Type of contact	Pneumatic contact
Description of the contact	Without shut-off Straight
Features	The Han® Pneumatic contacts without shut-off are suitable for the use inside a vacuum. (Limit: 100 mbar = 100 hPa ≈ approx 90% vacuum)

### Version

Gender	Female
Manufacturing process	Turned contacts

### Technical characteristics

Limiting temperature	-40 ... +85 °C
Operating pressure	≤10 bar
Tube inner diameter	6 mm

### Material properties

Material (contacts)	Brass
Material (seal)	NBR
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained



**Pushing Performance**  
Since 1945

## Material properties

REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	b51e5b97-eeb5-438b-8538-f1771d43c17d
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

## Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
----------	--

## Commercial data

Packaging size	10
Net weight	11 g
Country of origin	Germany
European customs tariff number	39269097
eCl@ss	27440204 Contact for industrial connectors