

91508-1 ✓ ACTIVE

AMP

TE Internal #: 91508-1

Portable Crimp Tools, Premium Crimp Tooling, Not Releasable,
Not Adjustable, Fixed In Tool, TE Product Specification (114-)

[View on TE.com >](#)



Application Tooling > Portable Crimp Tools



Tool Grade: **Premium Crimp Tooling**

Ratchet Configuration: **Not Releasable, Not Adjustable**

Die Sets Type: **Fixed In Tool**

Specification Type: **TE Product Specification (114-)**

TE Certification: **Yes – Certificate Included**

Features

Other

Crimp Form-Wire Barrel Type	Open Barrel - F Crimp
Tool Grade	Premium Crimp Tooling
Ratchet Configuration	Not Releasable, Not Adjustable
Die Sets Type	Fixed In Tool
Specification Type	TE Product Specification (114-)
TE Certification	Yes – Certificate Included
Power Technology Type	Battery, Electric, Manual
Tooling Type	CERTI-CRIMP II, Straight Action Hand Tool

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUL 2021 (219) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per

homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 350551-6
UMNL SOK 20-14 AU/PHBZ L/P



TE Part # 350551-7
UMNL SOK 20-14 AU/BR L/P



TE Part # 350538-7
UMNL PIN 20-14 AU/NI/BR



TE Part # 350919-3
UMNL SOK 18-14 PTPPHBZ



TE Part # 1-770005-0
UMNL II PIN AUSN/NI/BR



TE Part # 350551-1
UMNL SOK 20-14 PTPBR L/P



TE Part # 350551-3
UMNL SOK 20-14 PTPPHBZ L/P



TE Part # 350552-1
UMNL PIN 20-14 PTPBR L/P



TE Part # 350552-7
UMNL PIN 20-14 AUBR L/P



TE Part # 350918-3
UMNL PIN 18-14 PTPPHBZ



TE Part # 350551-2
UMNL SOK 20-14 AUBR L/P



TE Part # 350537-6
UMNL SOK 20-14 .0125 AUNI/PHBZ




TE Part # 350538-3
UMNL PIN 20-14 .0125 PTPPHBZ



TE Part # 350537-7
UMNL SOK 20-14 .0126 AUNI/BR



TE Part # 350537-3
UMNL SOK 20-14 .0125 PTPPHBZ



TE Part # 350873-3
UMNL PIN 18-14 .0125 PTPPHBZ



TE Part # 350874-3
UMNL SOK 18-14 .0125 PTPPHBZ



TE Part # 350873-1
UMNL PIN 18-14 .0126 PTPBR



TE Part # 350874-1
UMNL SOK 18-14 .0126 PTPBR



TE Part # 350538-1
UMNL PIN 20-14 .0126 PTPBR

Customers Also Bought



TE Part #91500-1
CCII UNML UNML II PIN SKT 20-14 ASSY



TE Part #1052604-1
2052 3123 00



TE Part #3-87631-0
34 MODIV HSG DR MRKD .100 POL



TE Part #5-1879208-8
CPF 0402 2K4 0.1% 25PPM 1K RL



TE Part #2-1879216-4
CPF 0402 88K7 0.1% 25PPM 1K RL



TE Part #2119143-1
CCII D1000 L REC TAB CONT 28-22 ASSY



TE Part #2305681-1
CCII HD1 HDC TAB REC 28-22 ASSY



TE Part #58380-2
AMP MNL 10 DIE SET

TE Part #1762129-1
SAHT DYNAMIC D4-L 14-12 ASSY

Documents



Datasheets & Catalog Pages

Bottoming Dies

English

[CERTI-CRIMP II TOOL DATA SHEET UNIVERSAL MATE-N-LOK CONTACT FAMILY](#)

English

Instruction Sheets

Instruction Sheet (U.S.)

English