

FEATURES

- Material: Steel structure
- DIN Rail
- IP66 protection against dust and powerful water jets
- IK10 protection against mechanical impacts
- Polyester epoxy powder coat textured finish
- Enclosure and door made from sheet steel
- The mounting plate is made from zinc-coated steel
- Lockable
- A single or double lock system
- Wall Mount
- Various sizes available

RS PRO Wall Boxes- Steel Wall Box

RS Stock No.: 915-5972



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO IP66 Metal Wall Boxes with Din Rail

Introducing a range of metal structure wall boxes from RS PRO. These boxes are incredibly useful, made from steel and are wall mountable. These boxes are rated at IP66 and provide an excellent degree of protection, whether it's used within an indoor or outdoor environment. RS PRO wall boxes are available in various sizes, suitable for a wide selection of applications.

General Specifications

Body Material	Steel
Number Of Doors	1
Colour	Grey
Gland Plate	Yes
Door Lock Type	Double Lock System
Chassis Plate	Yes
Transparent Door	No
Fixing Kit	Yes
Application	Electrical, Electronic, Industrial
External Mounting Type	Bracket
Internal Mounting Type	DIN Rail, Panel
Special Features	IK10 Against Mechanical Impacts
For Protection Of	Sensitive Electrical Equipment

Mechanical Specifications

External Height	800 mm
External Depth	210 mm
External Width	600 mm
Dimensions	H 800 mm x D 210 mm x W 600 mm

Protection Category

IP Rating	IP66
-----------	------

Approvals

Declarations	RoHS Certificate of Compliance
--------------	--------------------------------

Similar Products

Stock No.	Brand	Product Name	Colour	Body Material	Dimensions
775-5300	RS PRO	Steel Wall Box	Grey	Steel	300 mm x 250 mm x 150 mm
775-5788	RS PRO	Steel Wall Box	Grey	Steel	300 mm x 200 mm x 150 mm