

### **FEATURES**

- 7 x taps including thread sizes: M3, M4, M5, M6, M8, M10, M12
- 7 x drill pieces including sizes: 2.5mm, 3.3mm, 4.2mm, 5.0mm, 6.8mm, 8.5mm, 10.2mm
- Manufactured from high speed steel (HSS)
- Tolerance Class of Tap: 6H
- Suitable for a range of applications

# RS PRO HSS Tap & Drill Set

RS Stock No.: 917-2602



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

# **Threading Taps**



## **Product Description**

Introducing the 14 piece tap & drill set from our own brand RS PRO, a high quality compact set ideal for a variety of DIY tasks including cutting thread into materials and drilling holes when used with a hand or power tool such as a tap wrench or drill. The 14 piece set features a HSS (high speed steel) construction for enhanced durability and resistance to corrosion.

#### **General Specifications**

Туре	Threading Tap Set
Thread Standard	Metric
Contents	7pcs HSS ISO529 Straight Flute Tap: M3/M4/M5/M6/M8/M10/M12 7pcs HSS DIN338 Drills:2.5mm/3.3mm/4.2mm/5.0mm/6.8mm/8.5mm/10.2mm
Number of Pieces	14
Applications	Construction, DIY, Plumbing, Workshops, Renovations

#### **Mechanical Specifications**

Material	High Speed Steel
matoria:	riigir opoda otoor







