

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0936000022](#)  
**Status:** **Active**  
**Overview:** [GWconnect Heavy Duty Connectors \(HDC\)](#)  
**Description:** [GWconnect Metal Cable Gland - 5 Bar, for 19.00-36.00mm Cable, Pg36 Thread](#)

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Industrial Connectors / Enclosures
Series	<a href="#">93600</a>
Cable Gland Type	IP68 - 5 Bar
IP Rating	IP68
Overview	<a href="#">GWconnect Heavy Duty Connectors (HDC)</a>
Product Category	Cable Glands
Product Name	GWconnect
UPC	887191822549

**Physical**

Cable Diameter	19.00-36.00mm
Flammability	UL 94V-0
Material - Cable Gland	Brass
Material - Plating	Nickel
Net Weight	189.000/g
Packaging Type	Bag
Panel Cutout Diameter	47.50mm
Temperature Range - Operating	-40° to +125°C
Thread Size	Pg36
Thread Type	(Pg)
Waterproof / Dustproof	Yes
Waterproof / Dustproof Type	IP68

**Material Info**

Engineering Number	7000.6830.0
--------------------	-------------

**Reference - Drawing Numbers**

Sales Drawing	936000022-000
---------------	---------------



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2021)10043-DC (17  
Jan 2022)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

ZZCERT\_CE -

Declaration of

Conformity

**China RoHS**

Green Image

Not Relevant

Not Contained

CER\_4000400719\_00\_000.pdf

**Search Parts in this Series**

[93600 Series](#)

**Use With**

Industrial connector hoods and housings