

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0936000063](#)
Status: **Active**
Overview: [GWconnect Heavy Duty Connectors \(HDC\)](#)
Description: [GWconnect Metal Gable Gland - 5 Bar, for 4.00-10.00mm Cable, M16x1.5 Thread](#)

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Industrial Connectors / Enclosures
Series	93600
Cable Gland Type	IP68 - 5 Bar
IP Rating	IP68
Overview	GWconnect Heavy Duty Connectors (HDC)
Product Category	Cable Glands
Product Name	GWconnect
UPC	887191829852

Physical

Cable Diameter	4.00-10.00mm
Flammability	UL 94V-0
Material - Cable Gland	Brass
Material - Plating	Nickel
Net Weight	25.000/g
Packaging Type	Bag
Panel Cutout Diameter	16.50mm
Panel Mount	Yes
Temperature Range - Operating	-40° to +125°C
Thread Size	M16x1.5
Thread Type	(M) Metric
Waterproof / Dustproof	Yes
Waterproof / Dustproof Type	IP68

Material Info

Engineering Number 7000.6896.0

Reference - Drawing Numbers

Sales Drawing 936000063-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)10043-DC (17
Jan 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

ZZCERT_CE -

Declaration of

Conformity

China RoHS

Green Image

Not Relevant

Not Contained

CER_4000400719_00_000.pdf

Search Parts in this Series

[93600 Series](#)

Use With

Industrial connector hoods and housings