

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0936000355](#)
Status: **Active**
Overview: [GWconnect Heavy Duty Connectors \(HDC\)](#)
Description: [GWconnect Plastic Gable Gland, with Gasket, M25x1.5 Thread, Grey RAL 7001](#)

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Industrial Connectors / Enclosures
Series	93600
Cable Gland Type	IP68 with Gasket
IP Rating	IP68
Overview	GWconnect Heavy Duty Connectors (HDC)
Product Category	Cable Glands
Product Name	GWconnect
Standard	DIN EN 50262, EN 60529
UPC	887191852270

Physical

Cable Diameter	11.00-18.00mm
Flammability	UL 94V-2
Gland Color	Grey RAL 7001
Material - Cable Gland	Polyamide
Material - Gasket	NBR
Material - Nut	Polyamide
Net Weight	20.000/g
Packaging Type	Bag
Panel Cutout Diameter	25.50mm
Panel Mount	Yes
Temperature Range - Operating	-40° to +100°C
Thread Size	M25x1.5
Thread Type	(M) Metric
Waterproof / Dustproof	Yes
Waterproof / Dustproof Type	IP68

Material Info

Engineering Number	7000.7824.0
--------------------	-------------



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)10043-DC (17
Jan 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

ZZCERT_CE -

Declaration of

Conformity

China RoHS

Green Image

Not Relevant

Not Contained

CER_4000400719_00_000.pdf

Search Parts in this Series

[93600 Series](#)

Use With

Sealed Enclosures and Boxes