Cable Cutters ratchet action

(PATENTED)

- for cutting copper and aluminium single conductors as well as multiple stranded cables
- not suitable for steel wire and wire ropes
- precision ground, hardened blades
- clean and smooth cut without crushing and deformation
- one-hand operation using ratchet principle
- little handforce required due to very high transmission ratio
- two-stage ratchet drive for easy cutting
- simple handling as a result of low weight and compact design – can be used even in confined areas
- guard prevents operators' fingers being pinched
- High-grade special tool steel, forged, oil-hardened

95 36 280

suitable for aluminium sector cable up to 4 x 150 mm²





Ratchet principle and two-stage ratchet drive for easier cutting



95 36 250





					Cutting capacities			
	EAN				₩	₩		←→
Article No.	4003773-		Tool	Handles	Ø mm	mm²	MCM	mm
95 36 250	026884	☆ 1000 V △ ← ◆ 八八八 ★ ★	black lacquered	insulated with multi-component grips, VDE-tested	32	240	500	250
95 36 280	026891	≙ 1000 V △ ← ◆ ◆ ★ ★ ★ ★ ★ ★ ★ ★ ★ ★ ★ ★ ★ ★ ★ ★ ★ ★ 	black lacquered	insulated with multi-component grips, VDE-tested	52	380	750	280
95 39 250	022244	Movable spare blade for 95 31 250 / 95 36 250						
95 39 280	025283	Movable spare blade for 95 31 280 / 95 36 280						

Cable Cutter ratchet principle, 3-stage

Sturdy. Easy to use. Stable. Innovative ratchet-drive For cable up to 60 mm diameter



- easy handling due to low weight (830 g) and compact construction (320 mm length) – usable in confined areas also
- cutting through copper and aluminium cables with diameters of up to 60 mm in one-hand and two-hand operation
- hardened cutting edges, precisely ground, cut smoothly and neatly without crushing
- for cutting copper and aluminium single conductors as well as multiple stranded cables (not suitable for steel wire and wire ropes)
- innovative three-stage ratchet-drive with high leverage for easy cutting in one-hand and two-hand operation
- fixed handle with support area for putting down the pliers when cutting
- High-grade special tool steel, forged, oil-hardened

					Cutting capacities			
	EAN				₩	♦		↓ →
Article No.	4003773-		Tool	Handles	Ø mm	mm²	MCM	mm
95 36 320	075189	≙ 1000 V △ ← ◆ ///// ● (//// /// ///	black atramentized	insulated with multi-component grips, VDE-tested	60	600	1200	320
95 39 320 01	075714	Pivot cutter repair kit for 95 32 320 and 95 36 320						
95 39 320 02	075721	Fixed cutter repair kit for 95 32 320 and 95 36 320						