



97 21 215 Crimping Pliers



- Technical details
- Description
- Applications

	No.	97 21 215	
	EAN	4003773019688	
	Pliers	burnished	
	Handles	with multi-component grips	
	Applications	insulated terminals and plug connectors	
	Capacity	0,75 - 6,0	mm ²
	AWG	18 - 10	
	Number of crimping positions	3	
	Length	230	mm
	Net weight	290	g

- for cutting cables, stripping wire and crimping insulated and non-insulated terminals, connectors and plug type connectors
- with threaded holes for cutting copper and brass screws threaded M 2.6 / M 3 / M 3.5 / M 4 and M 5
- bolted joint for higher stability and even movement
- Special steel, high-strength





technical change and errors excepted