## **KNIPEX** Quality – Made in Germany



## **Product information**

## 97 52 18

## **Crimping Pliers**

For two-hand operation



# The ingenious lever transmission reduces the handforce up to 30% compared with regular crimping pliers Consistently biob crimping quality thanks to precision disc and force

- Consistently high crimping quality thanks to precision dies and forced locking mechanism (unlockable)
- Tools have been set precisely (calibrated) in the factory
- Two-hand operation for easy crimping of large conductor diametersEasy handling as a result of well balanced centre of gravity, angled
- head and ergnomically shaped handlesChrome vanadium electric steel in special quality, oil-hardened

#### General

Article No.	97 52 18
EAN	4003773026839
Pliers	burnished
Head	burnished
Handles	with non-slip plastic coating
Weight	571 g
Dimensions	250 x 78 x 26 mm
Reach	no
RohS	no

#### **Technical details**

w

Applications	Twin wire ferrules 2x6 / 2x10 / 2x16 mm <sup>2</sup>
Number of crimping positions	3
AWG	2 x 10 / 2 x 8 / 2 x 6

### Classification

endoemedation		
eCl@ss 5.1.4	21040301	
ETIM 5.0	EC000168	
ETIM 6.0	EC000168	
proficl@ss 6.0	AAA946c003	

technical change and errors excepted

## KNIPEX Quality – Made in Germany















## KNIPEX Quality – Made in Germany







