

## Product information

# 97 52 30 SB

## KNIPEX PreciForce®



- for solder-free electrical connections
- repetitive, high crimping quality due to precision dies and integral lock (self-releasing mechanism)
- tools have been set precisely (calibrated) in the factory
- high transmission of force thanks to lever action for fatigue-reduced working
- good handling thanks to favourable handle position, low weight, compact design and ergonomically shaped handles
- Chrome vanadium electric steel in special quality, oil-hardened

Allgemein	
Article No.	97 52 30 SB
EAN	4003773052586
Pliers	burnished
Handles	with multi-component grips
weight	499 g
Dimensions	220 x 84 x 25 mm

Technische Attribute	
Applications	non-insulated crimp connectors in accordance with DIN 46267
Capacity in square millimetres	1.5 — 4.0 mm <sup>2</sup>
Number of crimping positions	3
AWG	15 — 11

Klassifikation	
eCl@ss 5.1.4	21040301#
ETIM 5.0	EC000168
ETIM 6.0	EC000168
proficl@ss 6.0	AAA946c003

*technical change and errors excepted*