

Product information

97 52 33 SB

KNIPEX PreciForce®



- for solder-free electrical connections
- repetitive, high crimping quality due to precision dies and integral lock (self-releasing mechanism)
- tools have been set precisely (calibrated) in the factory
- high transmission of force thanks to lever action for fatigue-reduced working
- good handling thanks to favourable handle position, low weight, compact design and ergonomically shaped handles
- Chrome vanadium electric steel in special quality, oil-hardened

Allgemein

Article No.	97 52 33 SB
EAN	4003773052593
Pliers	burnished
Handles	with multi-component grips
weight	500 g
Dimensions	220 x 115 x 25 mm

Technische Attribute

Applications	non-insulated crimp terminals, tube and compression cable lugs in accordance with DIN 46234 and DIN 46235 and non-insulated crimp, butt and press connectors in accordance with DIN 46341 and DIN 46267
Capacity in square millimetres	0.5 — 10.0 mm ²
Number of crimping positions	4
AWG	20 — 7

Klassifikation

eCl@ss 5.1.4	21040301#
ETIM 5.0	EC000168
ETIM 6.0	EC000168
proficl@ss 6.0	AAA946c003

technical change and errors excepted