

SEFRAM9893 Carbon Monoxide(CO) Meter

■ Features :

- Large LCD dual displays for CO and TEMP measurement
- Backlight for easy screen viewing under dim lighting conditions
- Adjustable alarm limits
- CO level beeper can be silenced if desired
- Automatic Zero point adjustment
- MAX Hold function
- Data Hold function
- Auto Power Off
- Easy to replace battery
- Replaceable CO sensor extends tool life



General Specifications

Meas. Range	
CO	0 to 1000 ppm
Temperature	-20 to 70°C / -4 to 158°F
Resolution	
CO	1 ppm
Température	0,1°C / 0,1°F
Accuracy	
CO	5% or 5 ppm
Temperature	±0.8°C / ±1.5°F
Sensor Type	
CO	Stabilized electrochemical CO specific sensor;
Temperature	Thermistor temp sensor
Alarm limits	
Adjustable	
Sensor life	
3 years (typical)	
Power	
4 AA size battery	
Battery life	
200 hours (typical)	
Dimensions	
204 x 65 x 45 mm	
Weight	
235 g	

■ Applications

- Ambient air safety checks on residential appliance
- HVAC service on furnaces and hot water heaters
- Home inspections
- Industrial environments where the accumulation of CO is possible



For assistance and ordering

Sefram

32, rue Edouard Martel - BP55- 42009 - St Etienne - cedex 2
Tél. +33 (0) 4.77.59.01.01 / Fax. +33 (0) 4.77.57.23.23
Web : www.sefram.com - e-mail : sales@sefram.com



Follow us on :



FT SEFRAM9893 A00 - Specifications can be updated without notice

Visit our website: www.sefram.com