

Product datasheet

Specifications



modular single phase power meter iEM2000 - 230V - 40A

TSI code: 397406621 A9MEM2000

Main

Range	Acti 9
Family	Acti 9 iEM2000
Device short name	IEM2000
Product or component type	Energy meter

Complementary

Poles description	1P + N
Type of measurement	Active power
Device application	Sub billing
Accuracy class	Class 1 active energy conforming to IEC 62053-21
Input type	Direct input
Rated current	40 A
Rated voltage	230 V +/- 20 %
Network frequency	50 Hz 60 Hz
Frequency measurement range	48...62 Hz
Technology type	Electronic
Display type	Electromechanical
Sampling rate	32 samples/cycle
Measurement current	0...40 A
Display digits	7
Maximum value measured	999999.9 kWh
Communication port protocol	-
Communication port support	-
Local signalling	Green indicator light: power ON Yellow indicator light: metering and activity 3200 p/kWh
Digital inputs	0
Digital outputs	0
Maximum power consumption in VA	10 VA
Mounting mode	Clip-on

Mounting support	DIN rail
Connections - terminals	Power circuit: tunnel type terminals (bottom) 1 10 mm ² cable(s)
Tightening torque	Power circuit: 1.2 N.m
Standards	IEC 62053-21 IEC 61557-12
Product certifications	MID CE

Environment

IP degree of protection	IP40 conforming to IEC 60529
Ambient air temperature for operation	-20...70 °C -20...55 °C
Ambient air temperature for storage	-40...70 °C
Relative humidity	0...95 % at 55 °C
Colour	White
9 mm pitches	2
Width	18 mm
Height	95 mm
Depth	67 mm
Net weight	0.073 kg

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	115 g
Package 1 Height	3.2 cm
Package 1 width	7.2 cm
Package 1 Length	10 cm
Unit Type of Package 2	S02
Number of Units in Package 2	38
Package 2 Weight	4.711 kg
Package 2 Height	15 cm
Package 2 width	30 cm
Package 2 Length	40 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------
