

## SUMMARY



### # Wires

Low	0
High	0
Coax	1
Triax	0
Quad	0
Fiber	0
Fluidic	0

### Download

[Request a quote](#)

[Catalog](#)

Series	00
Termination type	Coupler/adapter/bridge
IP rating	50
Cable Ø	0.00 - 0.00 mm
Matching parts	FFA.00.250.NTAC22

## TECHNICAL DETAILS

### Mechanics

Shell Style/Model	ABA*: Adapter from LEMO receptacle to BNC plug
Keying	Circular (can rotate)
Housing Material	Brass (nickel plated) shell, collet nut, latch sleeve and mid pieces
Cable Fixing	∅ 0 - 0 mm
Variant	

### Performance

Configuration	0.25 : 1 Coax (50 Ohm)
Insulator	T: PTFE
Rated Current	4 Amps

### Specifications

Contact Type: Coaxial 50 Ohm  
Max. Matings: 500  
Contact Dia.: 0.7 mm (0.03in)  
Vtest: 2100 V (AC), 3000 V (DC)  
□  
Impedance: 50 Ohm  
VSWR: 1.09 + 0.11 \* f/GHz

## Others

Endurance (Shell): 5000 mating cycles


F ret (min): 100 N

IP Rating: 50

---

## DRAWINGS

### Draws



### Dimensions

	A	L	Weight
mm.	14.5	28.5	18.7
in.	0,57	1,12	0,74

---

## RECOMMENDED BY LEMO

### Tools

None

### Cables