

PRODUCT-DETAILS

M4M 30 ETHERNET

M4M 30 ETHERNET Network analyzer



General Information

Extended Product Type	M4M 30 ETHERNET
Product ID	2CSG274681R4051
EAN	8012542746812
Catalog Description	M4M 30 ETHERNET Network analyzer
Long Description	M4M 30 ETHERNET is a network analyzer with 4 programmable I/O, aux supply 48-240 V AC/DC, Bluetooth and Modbus TCP/IP

Technical

Meter Type	Digital
Mounting Type	Front panel (96x96 mm)
Dimensions	96 mm x 96 mm
Options Provided	40 individual harmonics
I/O Option	4 programmable I/O

Environmental

Ambient Air Temperature	Operation -25 ... +70 °C
RoHS Status	Following EU Directive 2011/65/EU

Dimensions

Product Net Width	96 mm
Product Net Height	96 mm
Product Net Depth / Length	77 mm
Product Net Weight	0.355 kg

Container Information

Package Level 1 Units	box 1 piece
Package Level 1 Width	135 mm
Package Level 1 Height	115 mm
Package Level 1 Depth / Length	170 mm
Package Level 1 Gross Weight	0.623 kg
Package Level 1 EAN	8012542746812

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	90303100

Certificates and Declarations (Document Number)

Declaration of Conformity - CE	9AKK107680A0174
Instructions and Manuals	2CSG445042D0201
RoHS Information	9AKK107680A0174

Popular Downloads

Data Sheet, Technical Information	9AKK107492A3557
Instructions and Manuals	2CSG445042D0201

Classifications

Object Classification Code	P
ETIM 6	EC001506 - Kilowatt-hour meter
ETIM 7	EC001506 - Kilowatt-hour meter

Categories

Low Voltage Products and Systems → Modular DIN Rail Products → Energy Efficiency Devices → Network Analyzers and Multimeters

