

## Brother ADS-1700W scanner ADF scanner 600 x 600 DPI A4 Black, White

**Brand :** Brother

**Product code:** ADS-1700W

**Product name :** ADS-1700W

LCD (touchscreen), 1200 x 1200 / 600 x 600 dpi, 25/50 ppm, 20 vel, Dual CIS, 802.11 b/g/n, 1 x Micro USB 3.0, 1.41 kg

Brother ADS-1700W scanner ADF scanner 600 x 600 DPI A4 Black, White:

With a 7.1cm LCD colour touchscreen and the ability to create up to 20 custom shortcuts to your frequently scanned-to destinations, the ADS-1700W is intuitive and easy to use. Its compact size is an ideal choice when desk space is limited, or place anywhere in the home or office and make use of its wireless connectivity feature using your mobile phone or tablet. With powerful paper-handling via the sheet-fed Automatic Document Feeder (ADF), 2-sided (duplex) documents, multi-page contracts or plastic ID cards can all be scanned quickly and easily.



Scanning		Power	
Maximum scan size *	215,9 x 863 mm	Power supply type *	AC
Optical scanning resolution *	600 x 600 DPI	Power consumption (typical)	9 W
Enhanced scan resolution	1200 x 1200 DPI	Power consumption (standby)	4,5 W
Colour scanning	✓	Power consumption (off)	0,1 W
Duplex scanning *	✓	AC input frequency	100 - 240 Hz
Input colour depth	48 bit	Sleep mode	✓
Output colour depth	24 bit	Input voltage	50 - 60 V
Greyscale levels	256	Power consumption (sleep)	1,6 W
ADF scan speed (b/w, A4)	25 ppm	Network	
ADF scan speed (colour, A4)	25 ppm	Wi-Fi	✓
Design		Wi-Fi standards	802.11b,802.11g,Wi-Fi 4 (802.11n)
Scanner type *	ADF scanner	Security algorithms	64-bit WEP,128-bit WEP,WPA-PSK,WPA2-PSK
Product colour *	Black, White	Wi-Fi Direct	✓
Display	LCD	Supported network protocols	DHCP, APIPA (Auto IP), WINS/NetBIOS name resolution, DNS Resolver, mDNS, LLNMR responder, SMTP Client, FTP/SFTP Client, CIFS Client, SNMPv1/v2c/v3, HTTP/HTTPS server, Web Services(Scan), ICMP, SNMP Client, RA
Display diagonal	7,11 cm (2.8")	Packaging data	
Touchscreen	✓	Package width	380 mm
Colour display	✓	Package depth	157 mm
Built-in display *	✓	Package height	200 mm
Performance		Package weight	1,9 kg
Sensor type *	Dual CIS		
Scan file formats	JPEG,PDF,TIFF		
Daily duty cycle (max) *	1000 pages		
Maximum duty cycle	10000 pages per month		
Scan to	E-mail, E-mail Server, FTP, File, Image, OCR, USB		
Scan drivers	ICA,SANE,TWAIN,WIA		
Barcode reader	✓		
Scanning noise level	62 dB		

Performance		System requirements	
Sound pressure level (max)	50 dB		Windows 10, Windows 10 Education, Windows 10 x64, Windows 10 Enterprise, Windows 10 Home, Windows 10 Home x64, Windows 10 IOT Core, Windows 10 Pro, Windows 10 Pro x64, Windows 7, Windows 7 Enterprise, Windows 7 Enterprise x64, Windows 7 Home Basic, Windows 7 Home Basic x64, Windows 7 Home Premium, Windows 7 Home Premium x64, Windows 7 Professional, Windows 7 Professional x64, Windows 7 Starter, Windows 7 Starter x64, Windows 7 Ultimate, Windows 7 Ultimate x64, Windows 8, Windows 8 Enterprise, Windows 8 Enterprise x64, Windows 8 Pro, Windows 8 Pro x64, Windows 8 x64
Internal memory	512 MB		Mac OS X 10.11 El Capitan, Mac OS X 10.12 Sierra, Mac OS X 10.13 High Sierra
Input capacity		Windows operating systems supported	
Auto document feeder (ADF) input capacity	20 sheets		
Paper handling		Mac operating systems supported	
Scanning media types supported	Business Card, Plain paper, Plastic Card, Thick paper	Linux operating systems supported	✓
Maximum ISO A-series paper size *	A4	Server operating systems supported	Windows Server 2008 R2, Windows Server 2012, Windows Server 2012 R2, Windows Server 2016
ISO A-series sizes (A0...A9)	A4		
Card thickness (max)	1,24 mm		
Auto Document Feeder (ADF) media weight	51 - 200 g/m <sup>2</sup>		
Maximum scan width	21,6 cm		
Maximum scan length	86,3 cm		
Ports & interfaces			
USB port *	✓		
USB version	3.2 Gen 1 (3.1 Gen 1)		
USB connector type	Micro-USB, USB Type-B		
Standard interfaces	USB 2.0, USB 3.2 Gen 1 (3.1 Gen 1), Wireless LAN		
Operational conditions			
Operating temperature (T-T)	5 - 35 °C		
Operating relative humidity (H-H)	20 - 80%		
Certificates			
Certification	GS Mark		
Weight & dimensions			
Width	300 mm		
Depth	103 mm		
Height	83 mm		
Weight	1,41 kg		
Packaging content			
Manual	✓		
Cables included	AC, USB		
Quick start guide	✓		
AC adapter included	✓		
Other features			
Web-based management	✓		
Technical details			
Sustainability certificates	ENERGY STAR		



012502652007

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.