

# DIGITUS Mini DisplayPort - VGA Adapter / Converter

AK-340407-001-W  
EAN 4016032289692



**DisplayPort adapter cable, mini DP - HD15 M/F, 0.15m, DP 1.1a compatible, CE, wh**

This adapter / converter suits for example ideal to connect a MacBook®, MacBook Air®, MacBook Pro®, iMac®, Mac Mini® and Mac Pro® to a VGA Monitor, beamer, LCD/TFT monitor with a VGA Monitor cable.

**Ensures a lower burden of the interface.**

- Support up to 1080p with 60Hz
- AWG: 32
- Interlock: none
- Connector surface: nickel-plated
- Color cable: white

- Color connector: white
- Hoods: molded
- Shielding: Double shielding
- Connector 1: Mini DP, plug
- Connector 2: HD15, jack
- DisplayPort standard: DisplayPort 1.1a
- Ferrite filter: none
- Assortment: DisplayPort Cables
- AOC - Active Optical Cable: no
- HDTV Standard: Full HD
- Length: 0.15 m
- Packaging: Polybag
- Wire material: CU

Logistics						
	Number (pcs)	Weight (kg)	Depth (cm)	Width (cm)	Height (cm)	cm³
Packaging Unit Carton	200	11.00	38.10	30.20	31.10	35,784.30
Packaging Unit Inside	10	0.55	40.60	40.60	8.10	13,351.70
Packaging Unit Single	1	0.06	20.00	15.00	1.62	486.00
Net single without Packaging	1	0.05	20.00	15.00	1.62	486.00

**More images:**



