



AK 03



AK 03

Small-scale distributors

CUSTOMIZE

100 x 150 x 96 mm
Article number: 73540301

Small-scale distributors, 3 distribution units, PE/N terminal, with each 1 clamping point 16 mm², 3 clamping points 6 mm², 3 elastic entries on top, masking and labelling strips, insulating seals, additional double-membrane seals



Technical data

Measures

Width:	100 mm
Length:	150 mm
Height:	96 mm
Inner height:	95 mm

Material:

Box:	Polystyrene, light grey, similar to RAL 7035
Cover:	Polystyrene, light grey, similar to RAL 7035
Sealing:	Polyurethane
Cover screw:	Polyamide 6, fiber-glass reinforced
material:	polystyrene
Hinged window:	Polycarbonate, transparent

Highlights

Reliable - The high protection class (IP65) and the robust, halogen-free design ensure reliable operation even in a tough industrial environment.

Accessory

- AK SGA-1 - Lock fittings
- BST M20/sw - Ventilation seal
- AK AS - Masking off strips
- BST M20 - Ventilation seal

Environmental attributes

Ambient temperature (min.):	-25 °C
Ambient temperature (max.):	40 °C
Ambient temperature (24 h):	35 °C
Max. rel. humidity at 25° C (short term):	95%
Max. rel. humidity at 40° C:	50%



AK 03

Other attributes

Color:	Grey
Ingress protection:	IP65 - acc. to EN 60529 / DIN VDE 0470-1
Number of distribution units:	3
Tackable:	No
Heavy metals-free:	Yes
PVC-free:	Yes
Silicone-free:	Yes
EMC design:	No
with lock:	No
sealable:	Yes
Impact resistance:	IK07 acc. DIN EN 5012 / VDE 0470 Part 100
Cover screw torque:	1.2 N m