



AK 09



AK 09

Small-scale distributors

CUSTOMIZE

200 x 200 x 122 mm
Article number: 73540901

Small-scale distributors, 9 distribution units, PE/N terminal, with each 2 clamping points 16 mm², 5 clamping points 6 mm², 6 elastic entries on top, masking and labelling strips, insulating seals, additional double-membrane seals



Technical data

Measures

| | |
|---------------|--------|
| Width: | 200 mm |
| Length: | 200 mm |
| Height: | 122 mm |
| Inner height: | 95 mm |

Material:

| | |
|----------------|--|
| Box: | Polystyrene, light grey, similar to RAL 7035 |
| Cover: | Polystyrene, light grey, similar to RAL 7035 |
| Sealing: | Polyurethane |
| Cover screw: | Polyamide 6, fiber-glass reinforced |
| material: | polystyrene |
| Hinged window: | Polycarbonate, transparent |

Highlights

Reliable - The high protection class (IP65) and the robust, halogen-free design ensure reliable operation even in a tough industrial environment.

Accessory

- AK SGA-1 - Lock fittings
- BST M20/sw - Ventilation seal
- AK AS - Masking off strips
- BST M20 - Ventilation seal

Environmental attributes

| | |
|---|--------|
| Ambient temperature (min.): | -25 °C |
| Ambient temperature (max.): | 40 °C |
| Ambient temperature (24 h): | 35 °C |
| Max. rel. humidity at 25° C (short term): | 95% |
| Max. rel. humidity at 40° C: | 50% |



AK 09

Other attributes

| | |
|-------------------------------|---|
| Color: | Grey |
| Ingress protection: | IP65 - acc. to EN 60529 / DIN VDE 0470-1 |
| Number of distribution units: | 9 |
| Tackable: | Yes |
| Heavy metals-free: | Yes |
| PVC-free: | Yes |
| Silicone-free: | Yes |
| EMC design: | No |
| with lock: | No |
| sealable: | Yes |
| Impact resistance: | IK07 acc. DIN EN 5012 / VDE 0470 Part 100 |
| Cover screw torque: | 1.2 N m |