SANITIZABLE COMPACT HYGIENE KEYBOARD WITH NUMPAD AK-C7000 SERIES MEDICAL KEY





FEATURES & BENEFITS

- + Hygiene Keyboard for Clinical Wipe Disinfection
- + Clinical Wipe Disinfection with all common Disinfectants according to German Guidelines VAH/DGHM
- + Utmost Writing Comfort by Scissors Balancing Technology
- + Perfect Type Writing in Hygiene Critical Applications
- Exchangeable Membrane for Machine Reprocessing: Maschine Reprocessing at 93°C and 134°C (in Addition to Wipe Disinfection) or optional:
 Wireless: Fully Sealed Membrane for Protection Class IP68
 Cabled: Fully Sealed IP68
 Backlit: Fully Sealed IP68
- + Clean-Function allows to switch off Keys during Cleaning Process

TECHNICAL DATA	ি	1)	- * -	
Compatibility	Х	×	Х	All systems, supporting a standard USB
Temperature Range	Х	X	Х	Storage –20° to +60°C; Operation 0° to +50°C
Silicon Keyboard Cover	Х	X	Х	Exchangeable Silicone Membrane (Standard) or Fully Sealed IP68 (Option)
Interface		X	Х	USB 1.1
	х			6 V via 4 AAA-Batteries
Supply Voltage		X	×	5 V +5%/-10% through USB Port
Current Consumption	х			10 mA (USB Low Power Device) / USB Type A (USB Nano-Dongle), Effective Range appr. 10m (2,4 GHz RF)
		X	Х	Backlit: Max. 169mA; Non-Backlit: Max. 25mA (USB Low-Power-Device)
Dimensions		X	х	Appr. 374 x 139 x 25mm
Dimensions	Х			Appr. 372 x 137 x 37mm
Weight	Х	X	х	730g
Dimming Backlight			Х	8 levels, intensity controlled by "FN" + Cursor "UP" and "Down" keys
LED Status Indicators	х	х	х	Caps Lock, Num Lock, Scroll Lock, CleanFunction
Key Travel / Actuation Force	Х	X	х	Ca. 2,5 +/- 0,5 mm / ca. 60g - similar to Notebook-Keyboards
Agency Approvals	Х	X		CE, RoHS, FCC Test-Report, EN-60601-1-2:2015 (IEC 4th Edition)*

<u>*No Medical Device acc.to MDR 2017/745 EU</u> PART NO. / ORDER NO.

Example: Keyboard AK-C7000 cabled, USB, White, German	AK-C7000F-U1	-	W	-	GE
Cabled, USB Interface, wipe disinfection, standard	AK-C7000F-U1	-	У	-	Х
Cabled, USB-Interface, fully sealed, IP68	AK-C7000F-UVS	-	у	-	х
Wireless interface, wipe disinfection, standard	AK-C7000F-FU1	-	у	-	×
Wireless Interface, fully sealed, IP68 with closed battery compartment	AK-C7000F-FUS	-	у	-	x
Backlit, cabled, USB Interface, wipe disinfection standard	AK-C B 7000F-U1	-	у	-	х
Backlit, cabled, USB Interface, fully sealed IP68	AK-C B 7000F-US	-	у	-	×
Exchangeable Membrane	AK-C7000	-	у	-	×
Exchangeable Membrane, Backlit	AK-C B 7000	-	у	-	X

Identifier z Version/Option	Identifier y Color	Identifier x Country Version	
Version: Cabled* U1 = USB-Connector, wipe disinfection (Standard Version) UVS = Fully Sealed, Protection Class IP68, USB US = Fully Sealed, Protection Class IP68, USB, Backlit	W = White (Standard Version) B = Black	GE = German FR = French UK = UK English	
Version: Wireless FU1 = Wireless, wipe disinfection (Standard Version) FUS = Wireless, fully sealed, Protection Class IP68 with closed battery compartment, USB Nano-Dongle		All other European country layouts are available at Active Key	

All trademarks are the property of their respective companies. Technical data is subject to change without notice. Errors and omissions excepted. Warranties excluded. AK is a trademark of Active Key GmbH. Active Key GmbH Brunnenäcker 6 91257 Pegnitz Deutschland Phone: +49 9241 / 48 33 7 - 0 Fax: +49 9241 / 48 33 7 - 29 E-Mail: info@activekey.de Web: www.activekey.de

Datasheet AK-C7000 29-04-20