

Amplified Indoor Radio Antenna 30 dB AM / FM

General information

Universal indoor antenna for the reception of AM and FM stereo radio signals.

Specifications

Power consumption in operating mode:	30 W
Frequency range:	87-108 MHz
Operating distance:	0-15 km
Impedance:	75 Ohm
Cable length:	1.1 m
Gain:	30 dB
Colour:	Black
Length:	1.1 m
Type:	Amplified
Input voltage:	220-240 VAC
Input voltage:	
Signal type:	AM
Signal type:	FM
Usage:	Indoor
Power plug:	Euro / Type C (CEE 7/16)
Application:	Radio
Connector type:	IEC Male

Package contents

1x Antenna
1x Manual



Sales information

Order code: **ANT 118-KN**
 Product description: Amplified Indoor Radio Antenna 30 dB AM / FM
 Packaging: Giftbox
 Brand name: König



Quantity	LxWxH (mm)	Weight
1	125x445x135	636 gr.
12	415x470x500	8500 gr.