



CU34P2A

34 inch (86.4 cm) LCD MONITOR

Productivity, connectivity, and comfort in a curved 1500R 34" ultra wide QHD display

1ms



ADJUSTABLE
STAND



FLICKER FREE



LOW BLUE MODE



VA PANEL

100Hz



WQHD-Auflösung



Mit 3440 x 1440 Auflösung bietet Wide Quad HD (WQHD) überragende Bildqualität und scharfe Bilder, die jedes Detail zeigen. Das Widescreen-Seitenverhältnis von 21:9 eignet sich ideal zum Ansehen von Filmen in einem großen Format oder um in ein spannendes Spiel einzutauchen, zudem bietet es mehr Platz, wenn es Zeit ist zu arbeiten. Echte 8-Bit-Farbe bietet eine breite Farbpalette für lebendige, natürlich wirkende Bilder.



Drei-Jahres-Garantie

AOC steht hinter der Qualität jedes einzelnen Monitors und bietet daher eine großzügige Drei-Jahres-Garantie ab dem ursprünglichen Kaufdatum. Innerhalb der Garantiezeit werden alle AOC-Displays mit Herstellungsfehlern oder fehlerhaften Komponenten repariert oder ohne zusätzliche Kosten ersetzt. Lesen Sie dazu die [komplette AOC-Garantieerklärung](#).



Flicker Free

Die AOC Flicker-Free Technologie nutzt ein DC (Gleichstrom) Panel mit Hintergrundbeleuchtung, das flackerndes Licht verringert. Augenbelastungen und -ermüdungen werden auf ein Minimum reduziert, daher können Sie lange, intensive Spielsitzungen komfortabel genießen!



Low Blue Light-Modus

Kurzwelliges blaues Licht kann den Augen schaden. Die AOC Low Blue Light-Technologie blockiert schädliche blaue Lichtstrahlen, ohne dass sich dadurch die dargestellte Farbe ändert. Andere Verfahren zum Reduzieren von blauem Licht verwenden Filter oder veränderte Einstellungen, was jedoch zu dunklen/gelblichen Bildern führt.



Wide viewing angle

Das Merkmal "Wide Viewing Angle" ermöglicht eine exakte Farbdarstellung bei einem großen Betrachtungswinkel von bis zu 178°. Auf diese Weise werden die Farben unabhängig von Ihrer Blickrichtung stets perfekt dargestellt.



Ergonomie

Fühlen Sie den Komfort! Die höhenverstellbaren, neig- und schwenkbaren Ständer von AOC helfen dabei, die komfortabelste und gesündeste Position zu ermitteln.

General

Model name	CU34P2A
EAN	4038986118224
Product Line	Pro-Line
Series	P2
Channel	B2B
Classification	Held
Section	Profianwender
Launch date	01-07-2020

Screen

Resolution	3440x1440 PX
Refresh rate	100Hz
Screen size (inch)	34 inch
Screen size (cm)	86.4 cm
Flat / Curved	Ja
Curvature Radius	1500 mm
Backlight	WLED
Panel Type	VA
Aspect ratio	21:9
Display Colours	16,7 Millionen
Panel Colour in Bits	8
sRGB Coverage (%)	120
Adobe RGB Coverage (%)	89
NTSC coverage (%)	85 %
Active Screen Area (HxW)	797.22(H) mm x 333.72(V) mm mm
Pixel Pitch	0.2745
Scanning Frequency	VDP1.2/HDMI2.0: 48~100Hz(V) DP1.2/HDMI2.0: 30~160KHz(H)
Response Time (MPRT)	1 ms
Contrast (static)	3000:1
Contrast (dynamic)	50M:1
Brightness (typical)	300 cd/m ²
Viewing angle (CR10)	178/178 °
Hard Glass	Antiglare + 3H
OSD languages	EN, FR , ES, PT, DE, IT, NL, SE, FI, PL ,CZ, RU, KR, CN (T), CN (S), JP

Exterior

Monitor colour	Schwarz
Bezel Type	Frameless
Removable Stand	✓

Ergonomics

Vesa Wallmount	100 x 100
Tilt	5.5° ±1° ~ 22° ±1.5° °
Swivel	180 °
Height Adjust Amount	150mm

Multimedia

Audio Input	Line in
Built-in Speakers	3 W x 2
Audio output	Headphone out (3,5mm)

Connectivity and Multimedia

Signal Input	HDMI 2.0 x 2, DisplayPort 1.2 x 1
USB input	USB 3.2 (Gen1) x 4
USB Hub	✓
USB out ports	4
USB fast charge	✓

What's in the Box?

HDMI cable	1,8 m
Displayport Cable	1,8 m
Power Cable C13	1,8 m

Power / Environmental

Powersupply	Intern
Powersource	100 - 240V, 50/60Hz
PowerConsumption On (Energystar)	55 watt
PowerConsumption Standby (Energystar)	0.5 watt
PowerConsumption Off (Energystar)	0.3 watt
EnergyClass	C

Approbations / Regulations

Listed on Energystar Website	✓
TCO	8
CE	✓
Rohs compliant	✓
Reach compliant	✓

Warranty

Warranty Period	3 Jahre
-----------------	---------

Dimensions / Weights

Product dimensions incl base	611.53(H)X808.34(W)X275.13(D)
Product dimensions excl base	367.45(H)X808.34(W)X100.14(D)
Packaging Dimensions (L x W x H)	903(W) x 250(D) x 527(H) mm
Product Dimensions (incl base)	611.53(H)X808.34(W)X275.13(D) mm
Gross Weight (including package)	12.7 Kg
Net Weight (excluding package)	9.8 Kg

Texts and USP

Marketing title	34 inch VA DisplayPort 1.2 x 1, HDMI 2.0 x 2 USB 3.2 (Gen1) x 4 AdaptiveSync
-----------------	--

Features

Sync Technology	AdaptiveSync
Flicker-free	✓
Blue Light Technology	Low blue light
Kensington Lock	✓