



Overview

| | |
|----------------------|---|
| Model Name | RACK ATS, 230V, 10A, C14 IN, (12) C13 OUT |
| Includes | Mounting Hardware , Rack Mounting brackets , Serial configuration cable |
| Standard Lead Time | Usually in Stock |
| Product Distribution | Afghanistan , Albania , Algeria , Andorra , Angola , Anguilla , Antigua And Barbuda , Argentina , Armenia , Aruba , Australia , Austria , Azerbaijan , Bahamas , Bahrain , Bangladesh , Barbados , Belarus , Belgium , Belize , Benin , Bermuda , Bhutan , Bolivia , Bosnia And Herzegovina , Botswana , Brazil , Brunei Darussalam , Bulgaria , Burkina Faso , Burundi , Cambodia , Cameroon , Canada , Cayman Islands , Central African Republic , Chad , Chile , Colombia , Congo , CONGO , THE DEMOCRATIC REPUBLIC OF THE , Cook Islands , Costa Rica , Cote D'Ivoire , Croatia , Cuba , Cyprus , Czech Republic , Denmark , Djibouti , Dominica , Dominican Republic , East Timor , Ecuador , Egypt , El Salvador , Equatorial Guinea , Eritrea , Estonia , Ethiopia , Falkland Islands (Malvinas) , Fiji , Finland , France , Gabon , Gambia , Georgia , Germany , Ghana , Gibraltar , Greece , Grenada , Guadeloupe , Guatemala , Guinea , Guyana , French Guiana , Haiti , Honduras , Hungary , Iceland , India , Indonesia , Iran (Islamic Republic Of) , Iraq , Ireland , Israel , Italy , Jamaica , Jordan , Kazakhstan , Kenya , KOREA, REPUBLIC OF , Kuwait , Latvia , Lebanon , Lesotho , Liberia , Liechtenstein , Lithuania , Luxembourg , Macedonia , Madagascar , Malawi , Malaysia , Mali , Malta , Martinique , Mauritania , Mauritius , Mayotte , Mexico , Moldova, Republic Of , Mongolia , Morocco , Mozambique , Myanmar , Namibia , Nepal , Netherlands , Netherlands Antilles , New Zealand , Nicaragua , Niger , Nigeria , Norway , Oman , Pakistan , Panama , Papua New Guinea , Paraguay , Peru , Philippines , Poland , Portugal , Puerto Rico , Qatar , Reunion , Romania , Russian Federation , Rwanda , SAINT KITTS AND NEVIS , SAINT LUCIA , SAINT VINCENT AND THE GRENADINES , Saudi Arabia , Senegal , Sierra Leone , Singapore , Slovakia (Slovak Republic) , Slovenia , Somalia , South Africa , Spain , Sri Lanka , Sudan , Suriname , Sweden , Switzerland , Tajikistan , TANZANIA, UNITED REPUBLIC OF , Thailand , Togo , Trinidad And Tobago , Tunisia , Turkey , Turkmenistan , Turks And Caicos Islands , Uganda , Ukraine , United Arab Emirates , United States , Uruguay , Uzbekistan , Venezuela , Viet Nam , VIRGIN ISLANDS (UNITED STATES) , Western Sahara , Yemen , Zambia , Zimbabwe |

Output

| | |
|--------------------------------------|-----------------------------------|
| Nominal Output Voltage | 230V |
| Maximum Total Current Draw per Phase | 10 A |
| Output Connections | (12) IEC 320 C13 (Battery Backup) |
| Overload Protection | No |

Input

| | |
|-----------------------|----------|
| Nominal Input Voltage | 230V |
| Input Frequency | 50/60 Hz |

| | |
|---------------------------------|-------------|
| Input Connections | IEC-320 C14 |
| Maximum Line Current per phase | 10 A |
| Maximum Input Current per phase | 10 A |
| Load Capacity | 2000 VA |

Physical

| | |
|-----------------|----------|
| Net Weight | 3.93 kg |
| Maximum Height | 44.0 mm |
| Maximum Width | 432.0 mm |
| Maximum Depth | 236.0 mm |
| Shipping Weight | 5.7 kg |
| Shipping Height | 114.0 mm |
| Shipping Width | 600.0 mm |
| Shipping Depth | 349.0 mm |
| Color | Black |

Environmental

| | |
|-----------------------------|----------------|
| Operating Environment | -5 - 45 °C |
| Operating Relative Humidity | 5 - 95 % |
| Operating Elevation | 0-3000 meters |
| Storage Temperature | -25 - 65 °C |
| Storage Relative Humidity | 5 - 95 % |
| Storage Elevation | 0-15000 meters |

Conformance

| | |
|-------------------|--|
| Approvals | EN 55022 Class A , FCC Part 15 Class A |
| Standard warranty | 2 years repair or replace |

Sustainable Offer Status

| | |
|--------------------------------|--------------------------|
| RoHS | Compliant |
| REACH | REACH: Contains No SVHCs |
| Battery Directive | Compliant |
| Other Environmental Compliance | China RoHS |