

Product data sheet

Specifications



Rack PDU, Basic, 0U/1U, 100-240V/20A, 220-240V/16A, (7) C13, (2) C19

AP6120A

Overview

Lead time Usually in Stock

Main

Main Input Voltage 100 V
120 V
200 V
208 V
230 V
240 V

PDU Type Basic

Main Output Voltage 100 V
120 V
200 V
208 V
230 V
240 V

Input Connection Type IEC 60320 C20

Number of rack unit 1U

Provided Equipment Installation guide
Safety guide

Physical

Height 1.73 in (4.4 cm)

Width 15.28 in (38.8 cm)

Depth 3.66 in (9.3 cm)

Net Weight 3.44 lb(US) (1.56 kg)

Mounting Location Front
Rear

Mounting preference No preference

Mounting Mode Not rack-mountable

USB compatible No

Mounting position Horizontal

Input

Line Rated Current 16 A

Permissible voltage 100...240 V

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Max line current	20 A
Input current limits	20 A
Load Capacity	2300 VA
Input Frequency	50/60 Hz

Output

Number of power socket outlets	7 IEC 60320 C13 2 IEC 60320 C19
--------------------------------	------------------------------------

Conformance

Product Certifications	cUL Listed CE EAC IRAM PSE UL Listed VDE
------------------------	--

Ordering and shipping details

GTIN	731304327851
------	--------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.27 in (21 cm)
Package 1 Width	2.99 in (7.6 cm)
Package 1 Length	17.17 in (43.6 cm)
Package 1 Weight	4.45 lb(US) (2.02 kg)
SCC14	50731304327856

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Recommended replacement(s)