

# Product datasheet

Specifications



## Rack PDU, Basic, Zero U, 16A, 230V, (20) C13 & (4) C19, IEC C20

AP7552

### Overview

Lead time Usually in Stock

### Main

Main Input Voltage	200 V 208 V 230 V
PDU type	Basic
Main Output Voltage	230 V
Input Connection Type	IEC 60320 C20
Number of rack unit	0U
Cable length	3.05 m
Number of cables	1
Provided equipment	Installation guide Rack mounting brackets Toolless mounting kit

### Physical

Colour	Black
Height	161.9 cm
Width	5.6 cm
Depth	4.4 cm
Net weight	4.86 kg
Mounting location	Side
Mounting preference	No preference
Mounting mode	Rack-mounted
Mounting position	Vertical

### Input

Input current limits	16 A
Load capacity	3680 VA
Network frequency	50/60 Hz

## Output

Number of power socket outlets	20 IEC 60320 C13 4 IEC 60320 C19
--------------------------------	-------------------------------------

## Conformance

Product certifications	CE GOST IRAM VDE
------------------------	---------------------------

## Environmental

Ambient air temperature for operation	0...45 °C
Relative humidity	5...95 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-25...65 °C
Storage Relative Humidity	5...95 %
Storage altitude	0.00...15240.00 m

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	212.1 cm
Package 1 Width	15.2 cm
Package 1 Length	12.7 cm
Package 1 Weight	5.758 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Lead free	Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

## Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

## Recommended replacement(s)