

# Product data sheet

Specifications



## Rack PDU, Switched, 1U, 12A/208V, 10A/230V, (8)C13



AP7920B

### Overview

#### Presentation

This APC Switched Rack PDU power distribution unit has a wide range of standardized PDU features that increase network efficiency, manageability and functionality. The output and input connections are (8)C13. Network management capabilities allow you to configure and manage rack PDUs from remote locations. It has a local current monitoring display that gives a visible warning in case of an overload. The remote individual outlet control provides real-time monitoring of connected loads. It has a multi-tier user access that enables you to restrict unauthorized use of outlets. This rack has a single input power source making it easy to install.

#### Lead time

Usually in Stock

### Main

#### Main Input Voltage

200 V  
208 V  
230 V

#### Main Output Voltage

208 V  
230 V

#### Input Connection Type

IEC 60320 C14

#### Number of rack unit

1U

#### Cable length

6.5 ft (1.98 m)

#### Number of cables

1

#### Provided Equipment

Installation guide  
Rack Mounting brackets  
User Manual

### Physical

#### Color

Black

#### Height

1.73 in (4.4 cm)

#### Width

17.52 in (44.5 cm)

#### Depth

4.25 in (10.8 cm)

#### Net Weight

5.00 lb(US) (2.27 kg)

#### Mounting Location

Front  
Rear

#### Mounting preference

No preference

#### Mounting Mode

Rack-mounted

### Input

#### Line Rated Current

12 A

Acceptable Input Voltage	200...240 V
Input current limits	15 A
Load Capacity	2300 VA
Input Frequency	50/60 Hz

## Output

Different voltages and corresponding amperages	10 A - 230 V 12 A - 208 V
Number of power socket outlets	8 IEC 60320 C13

## Conformance

Product Certifications	cUL Listed CE CSA GOST IRAM UL Listed VDE
Standards	EN 55022 Class A EN 55024 EN 61000-3-2 EN 61000-3-3 UL 60950

## Environmental

Ambient air temperature for operation	32...113 °F (0...45 °C)
Relative Humidity	0...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

## Ordering and shipping details

GTIN	731304331612
Package weight(Lbs)	7.61 lb(US) (3.45 kg)

## Packing Units

Package 1 Height	2.76 in (7 cm)
Package 1 width	18.50 in (47 cm)
Package 1 Length	13.50 in (34.3 cm)

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

<b>Circularity Profile</b>	<a href="#">End of Life Information</a>
<b>Optimized Energy Efficiency</b>	Energy efficient product
<b>Take-back</b>	Take-back program available
<b>Contractual warranty</b>	
<b>Warranty</b>	2 years repair or replace