



APC Replacement Battery Cartridge #113 with 2 Year Warranty

APCRBC113

Call for More Information

- Includes: All required connectors, Battery recycling guide, Installation guide, Reusable packaging

Output

Battery Capacity (mAh)	7000
Battery Output Voltage	24 V

Batteries & Runtime

Battery type	Lead-acid battery
Battery mounting	Enclosed battery cartridge
Expected Battery Life (years)	3 - 5
RBC Quantity	1

Physical

Maximum Height	102MM, 10.2CM
Maximum Width	133MM, 13.3CM
Maximum Depth	152MM, 15.2CM
Net Weight	6.8KG
Shipping weight	7.0KG
Shipping Height	140MM, 14.0CM
Shipping Width	171MM, 17.1CM
Shipping Depth	210MM, 21.0CM
Color	Black

Environmental

Operating Temperature	0 - 40 °C
-----------------------	-----------

Disclaimer: Documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user's applications.

Technical Specifications

Environmental	
Operating Relative Humidity	0 - 95 %
Operating Elevation	0 - 3048meters
Storage Temperature	-5 - 45 °C
Storage Relative Humidity	0 - 95 %
Storage Elevation	0 - 15240meters

Conformance	
Standard warranty	2 years repair or replace

Sustainable Offer Status	
RoHS	Compliant
PEP	Available in Documentation tab
EOLI	Available in Documentation tab
Proposition 65 Warning	Available in Documentation tab

Disclaimer: Documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user's applications.