

Product data sheet

Specifications



APC Replacement Battery Cartridge #116 with 2 Year Warranty

APCRBC116

Product availability : Stock - Normally stocked in distribution facility

Overview

Lead time Usually in Stock

Main

Product or Component Type Replacement battery cartridge

Battery Type Lead-Acid battery

Batteries & Runtime

Battery Placement Internal Battery

Battery Slots Empty 0

Included Battery Modules 0

Device mounting Enclosed battery cartridge

Battery Voltage 48V

RBC Quantity 1

Replacement battery

Physical

Color Black

Height 3.50 in (8.9 cm)

Width 6.50 in (16.5 cm)

Depth 16.50 in (41.9 cm)

Net Weight 23.04 lb(US) (10.45 kg)

Mounting Mode Not rack-mountable

Environmental

Ambient Air Temperature for Operation 32...104 °F (0...40 °C)

Operating altitude	0...10000 ft
Relative Humidity	0...95 %
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage altitude	0...50000 ft (0.00...15240.00 m)

Ordering and shipping details

Category	11309-APC RESALE PRODUCTS
Discount Schedule	APC1
GTIN	731304281696
Returnability	No
Country of origin	VN

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.48 in (19 cm)
Package 1 Width	11.50 in (29.2 cm)
Package 1 Length	21.50 in (54.6 cm)
Package 1 Weight	25.04 lb(US) (11.36 kg)
SCC14	731304281696

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Recommended replacement(s)