Product datasheet

Specifications



APC Replacement battery cartride #148 with 2 Year Warranty

APCRBC148

Overview

Lead time	Usually in Stock

Main

Main Input Voltage	12 V DC
Product or component type	Replacement battery cartridge
Number of cables	1
Battery type	Lead-acid battery
Provided equipment	All required connectors Battery recycling guide Metallic battery tray or enclosure Reusable packaging Installation guide

Batteries & Runtime

Number of battery free slots	0
Number of battery filled slots	0
Device mounting	Enclosed battery cartridge
Number of battery replacement quantity	1
Replacement battery	

Physical

Colour	Black
Height	8.3 cm
Width	21.6 cm
Depth	34.3 cm
Net weight	10 kg
Mounting mode	Not rack-mountable
USB compatible	No

Environmental

Ambient air temperature for operation	0…45 °C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Operating altitude	0...10000 ft
Relative humidity	0…95 %
Ambient air temperature for storage	-15…45 °C
Storage altitude	0.00…15240.00 m
Storage Relative Humidity	0…95 %

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	15.2 cm
Package 1 Width	49.5 cm
Package 1 Length	36.8 cm
Package 1 Weight	10.91 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACh Regulation	REACh Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Lead free	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace

Recommended replacement(s)