

Product datasheet

Specifications

APC Replacement Battery Cartridge 175



APCRBC175

Overview

Lead time Usually in Stock

Main

Main Input Voltage	12 V
Product or component type	Replacement battery cartridge
Main Output Voltage	12 V
Battery type	Lead-acid battery
Provided equipment	User manual

Batteries & Runtime

Battery location	Internal battery
Number of battery blocks per string	6
Number of battery free slots	0
Number of battery filled slots	0
Device mounting	Built-in
Battery voltage	12 V
Number of battery replacement quantity	1

Replacement battery

Physical

Colour	Black
Height	151 mm
Width	99 mm
Depth	65 mm
Net weight	2.68 kg
Mounting preference	No preference
Mounting mode	Not rack-mountable

Output

Battery capacity	9 Ah
------------------	------

Conformance

Product certifications	UL 1778 5th edition
------------------------	---------------------

Standards	UL 1778 5th edition
-----------	---------------------

Environmental

Ambient air temperature for operation	0...40 °C
---------------------------------------	-----------

Operating altitude	0...10000 ft
--------------------	--------------

Relative humidity	0...85 %
-------------------	----------

Ambient air temperature for storage	-15...50 °C
-------------------------------------	-------------

Storage altitude	0.00...3048.00 m
------------------	------------------

Storage Relative Humidity	0...95 %
---------------------------	----------

Packing Units

Unit Type of Package 1	PCE
------------------------	-----

Number of Units in Package 1	1
------------------------------	---

Package 1 Height	19.5 cm
------------------	---------

Package 1 Width	39.5 cm
-----------------	---------

Package 1 Length	49.5 cm
------------------	---------

Package 1 Weight	18 kg
------------------	-------

SCC14	50731304427198
-------	----------------

Offer Sustainability

REACH Regulation	REACH Declaration
------------------	-----------------------------------

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
-------------------	---------------------------------------------------------------------------------------------------

Mercury free	Yes
--------------	-----

China RoHS Regulation	China RoHS declaration
-----------------------	----------------------------------------

RoHS exemption information	Yes
----------------------------	---------------------

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Recommended replacement(s)