

Power Cord, C19 to CEE/7 Schuko, 2.5m

AP9875

Call for More Information 0800 2799254



| Output | |
|----------------------------|-------------------|
| Overload Protection | No |
| Maximum Total Current Draw | 16 |
| Output Connections | (1) IEC 60320 C19 |

| Input | |
|--------------------------|------------------------|
| Input frequency | 50/60 Hz |
| Input Connections | Schuko CEE 7 / EU1-16P |
| Cord Length | 2.5meters |
| Acceptable Input Voltage | 90 - 250VAC |
| Number of Power Cords | 1 |
| Maximum Input Current | 16A |
| Maximum Line Current | 16A |

| Physical | |
|-----------------|---------------|
| Net Weight | 0.22KG |
| Shipping weight | 0.3KG |
| Shipping Height | 51MM, 5.1CM |
| Shipping Width | 102MM, 10.2CM |
| Shipping Depth | 203MM, 20.3CM |
| Color | Black |

Disclaimer: Documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user's applications.

Technical Specifications

| Environmental | |
|-----------------------------|-----------------|
| Operating Temperature | 0 - 45 °C |
| Operating Relative Humidity | 0 - 95 % |
| Operating Elevation | 0 - 3048meters |
| Storage Temperature | -25 - 65 °C |
| Storage Relative Humidity | 0 - 95 % |
| Storage Elevation | 0 - 15240meters |

| Conformance | |
|-------------------|---------------------------|
| Approvals | VDE |
| Standard warranty | 2 years repair or replace |

| Sustainable Offer Status | |
|--------------------------|-----------|
| RoHS | Compliant |

Disclaimer: Documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user's applications.