

APC Replacement Battery Cartridge #135 with 2 Year Warranty

APCRBC135

Call for More Information 0800 2799254



- Includes: Installation guide

Output

Battery Capacity (mAh)	5000
Battery Output Voltage	24 V

Batteries & Runtime

Battery type	Lead-acid battery
Battery mounting	Stand alone battery stack
Battery Placement	Internal battery
Expected Battery Life (years)	3 - 5
RBC Quantity	1
Battery blocks per string	2

Physical

Maximum Height	107MM, 10.7CM
Maximum Width	107MM, 10.7CM
Maximum Depth	144MM, 14.4CM
Net Weight	4.68KG
Shipping weight	5.14KG
Shipping Height	229MM, 22.9CM
Shipping Width	229MM, 22.9CM
Shipping Depth	229MM, 22.9CM
Units per Pallet	100.0

Disclaimer: Documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user's applications.

Technical Specifications

Environmental	
Operating Temperature	0 - 40 °C
Operating Relative Humidity	0 - 95 %
Operating Elevation	0 - 3048meters
Storage Temperature	-15 - 45 °C
Storage Relative Humidity	0 - 95 %
Storage Elevation	0 - 15240meters

Conformance	
Standard warranty	2 years repair or replace

Sustainable Offer Status	
RoHS	Compliant
Proposition 65 Warning	Available in Documentation tab

Disclaimer: Documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user's applications.