



## APC Replacement Battery Cartridge #176

### APCRBC176

Call for More Information 0800 2799254

- Includes: User manual

Output	
Battery Capacity (mAh)	7000
Battery Output Voltage	24 V

Batteries & Runtime	
Battery type	Lead-acid battery
Battery mounting	Built-in
Battery Placement	Internal battery
Battery blocks per string	6

Physical	
Maximum Height	151MM, 15.1CM
Maximum Width	99MM, 9.9CM
Maximum Depth	132MM, 13.2CM
Net Weight	4.3KG
Shipping weight	18.9KG
Shipping Height	195MM, 19.5CM
Shipping Width	495MM, 49.5CM
Shipping Depth	395MM, 39.5CM
Color	Black

Environmental	
Operating Temperature	0 - 40 °C

Disclaimer: Documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user's applications.

## Technical Specifications

Environmental	
Operating Relative Humidity	0 - 85 %
Operating Elevation	0 - 3048meters
Storage Temperature	-15 - 50 °C
Storage Relative Humidity	0 - 95 %
Storage Elevation	0 - 3048meters

Conformance	
Approvals	UL 1778 5th edition
Standard warranty	2 years repair or replace

Sustainable Offer Status	
RoHS	Compliant
Other Environmental Compliance	China RoHS

**Disclaimer:** Documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user's applications.