



APC NetShelter SX, Server Rack Enclosure, 42U, Black, 1991H x 750W x 1200D mm

AR3350

Call for More Information 0800 2799254

- Wide enclosure with increased cable management options for high density server and networking applications. 42U height to easily roll through doorways.
- Includes: Baying hardware, Key(s), Keyed-alike doors and side panels, Leveling feet,
 Mounting hardware, Pre-installed casters, Side panels

Physical	
Maximum Height	1991MM, 199.1CM
Maximum Width	750MM, 75.0CM
Maximum Depth	1200MM, 120.0CM
Rack Height	42U
Net Weight	161.36KG
Shipping weight	183.18KG
Shipping Height	2118MM, 211.8CM
Shipping Width	851MM, 85.1CM
Shipping Depth	1334MM, 133.4CM
Color	Black
Maximum Mounting Depth	1048.0MM, 104.8CM
Minimum Mounting Depth	262.0MM, 26.19CM
Front Door	16.0gauge
Vertical Posts	16.0gauge
Rear Door	16.0gauge
Roof	18.0gauge
Side Panels	18.0gauge
Units per Pallet	1.0
Rack Width	19"
Weight Capacity (static load)	1700.97KG
Weight Capacity (dynamic load)	1020.58KG

Disclaimer: Documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user's applications.

Technical Specifications



APC NetShelter SX, Server Rack Enclosure, 42U, Black, 1991H x 750W x 1200D mm | AR3350 | Downloaded on 02/25/2022 (EST)

Environmental	
Protection Class	IP20
Conformance	
Approvals	EIA-310E, UL 2416, UL 60950-1
Standard warranty	5 year repair or replace
Sustainable Offer Status	
RoHS	Compliant

Disclaimer: Documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user's applications.