

## APC Service Bypass Panel- 230V; 32A; MBB; Hardwire input; (4) IEC-320 C19 Output SBP6KRM12U



Call for More Information 0800 2799254

- Includes: Installation guide, Rack mounting brackets, User manual

Output	
Nominal Output Voltage	230V
Efficiency at Full Load	99 % %
Overload Protection	Yes
Maximum Total Current Draw	32
Output Connections	(4) IEC 60320 C19

Input	
Nominal Input Voltage	230V
Input frequency	50/60 Hz
Input Connections	Hard wire 3-wire (1P + N + E)
Efficiency at Full Load	99 % %
Load Power Factor Range	0 to 1
Load Capacity	7680VA
Maximum Input Current	32A
Maximum Line Current	32A

Physical	
Maximum Height	89MM, 8.9CM
Maximum Width	432MM, 43.2CM
Maximum Depth	660MM, 66.0CM
Rack Height	2U
Net Weight	11.36KG

**Disclaimer:** Documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user's applications.

## Technical Specifications

Physical	
Shipping weight	22.72KG
Shipping Height	203MM, 20.3CM
Shipping Width	610MM, 61.0CM
Shipping Depth	991MM, 99.1CM
Color	Black

Environmental	
Operating Temperature	-20 - 50 °C
Operating Relative Humidity	0 - 95 %
Operating Elevation	0 - 4572meters
Storage Temperature	-40 - 65 °C
Storage Relative Humidity	0 - 95 %
Storage Elevation	0 - 15240meters

Conformance	
Approvals	CSA, EN 60950, GOST, IEC 60950, UL 1778
Standard warranty	2 years (parts only)

**Disclaimer:** Documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user's applications.