

Technical Specifications

APC Smart-UPS On-Line, 1000VA, Lithium-ion, Rackmount 3U, 230V, 8x C13 IEC outlets, Network Card, Extended runtime, W/ rail kit | SRTL1000RMXLI-NC | Downloaded on 10/03/2022 (EST)



APC Smart-UPS On-Line, 1000VA, Lithium-ion, Rackmount 3U, 230V, 8x C13 IEC outlets, Network Card, Extended runtime, W/ rail kit

SRTL1000RMXLI-NC

Call for More Information 0800 2799254

- High density, double-conversion on-line power protection with scalable runtime.
- Includes: CD with software, Communication cable, Documentation CD, Installation guide, Removable support feet, USB cable, Warranty card

Output	
Output power capacity	900 Watts / 1.0kVA
Max Configurable Power (Watts)	900 Watts / 1.0kVA
Nominal Output Voltage	230V
Output Voltage Distortion	Less than 2 %
Output Frequency (sync to mains)	50/60 Hz +/- 3 Hz Sync to mains
Other Output Voltages	220 V, 240 V
Load Crest Factor	3 : 1
Topology	Double conversion online
Waveform type	Sine wave
Output Connections	(8) IEC 60320 C13
Bypass	Built-in bypass

Input	
Nominal Input Voltage	230V
Input frequency	40 - 70 Hz Auto-sensing
Input Connections	IEC 60320 C14
Cord Length	1.8meters
Input voltage range for main operations	50 - 150 40% load, 80 - 150V
Number of Power Cords	1
Other Input Voltages	220 V, 240 V

Disclaimer: Documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user's applications.

Technical Specifications

APC Smart-UPS On-Line, 1000VA, Lithium-ion, Rackmount 3U, 230V, 8x C13 IEC outlets, Network Card, Extended runtime, W/ rail kit | SRTL1000RMXLI-NC | Downloaded on 10/03/2022 (EST)

Batteries & Runtime	
Battery type	Li-Ion (Lithium-Ion)
Typical recharge time	6hour(s)
Nominal Battery Voltage	48 V
Expected Battery Life (years)	5 - 10
Battery Charge Power (Watts)	103 Watts
Extendable Run Time	1
Battery Volt-Amp-Hour Capacity	585
Runtime	View Runtime Graph (Available in Technical Tab on site)

Communications & Management	
Interface Port(s)	RJ-45 10/100 Base-T, RJ-45 Serial, Smart-Slot, USB
Control panel	Multifunction LCD status and control console
Audible Alarm	Audible and visible alarms prioritized by severity
Emergency Power Off (EPO)	Yes

Surge Protection and Filtering	
Surge energy rating	340Joules

Physical	
Maximum Height	128MM, 12.8CM
Maximum Width	432MM, 43.2CM
Maximum Depth	590MM, 59.0CM
Rack Height	3U
Net Weight	26.7KG
Shipping weight	46.86KG
Shipping Height	445MM, 44.5CM
Shipping Width	600MM, 60.0CM
Shipping Depth	850MM, 85.0CM
Color	Black
Units per Pallet	6.0

Disclaimer: Documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user's applications.

Technical Specifications

APC Smart-UPS On-Line, 1000VA, Lithium-ion, Rackmount 3U, 230V, 8x C13 IEC outlets, Network Card, Extended runtime, W/ rail kit | SRTL1000RMXLI-NC | Downloaded on 10/03/2022 (EST)

Environmental	
Operating Temperature	0 - 40 °C
Operating Relative Humidity	0 - 95 (Non-condensing) %
Operating Elevation	0 - 3048meters
Storage Temperature	-15 - 45 °C
Storage Relative Humidity	0 - 95 (Non-condensing) %
Storage Elevation	0 - 15240meters
Audible noise at 1 meter from surface of unit	50.0dBA
Online thermal dissipation	400.0BTU/hr
Protection Class	IP20

Conformance	
Approvals	CE, CE Mark, EAC, RCM, VDE
Standard warranty	5 year repair or replace

Sustainable Offer Status	
RoHS	Compliant

Disclaimer: Documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user's applications.