



APC Easy UPS On-Line SRV 3000VA 230V, Argentina.

SRV3KI

Call for More Information 0800 2799254

- High quality, Double-conversion On-line UPS designed for essential power protection needs even in the most unstable power conditions.
- Includes: Basic UPS signalling RS-232 cable, C13-C14 power cord, CD with software, IEC-C20 - Shuko input power cord, USB cable, User manual

Output	
Output power capacity	2.4kWatts / 3.0kVA
Max Configurable Power (Watts)	2.4kWatts / 3.0kVA
Nominal Output Voltage	230V
Output Voltage Note	Configurable for 220 : 230 or 240 nominal output voltage
Efficiency at Full Load	88.0 %
Output Voltage Distortion	3 %
Output Frequency (sync to mains)	50/60 Hz +/- 3 Hz Sync to mains
Other Output Voltages	220 V, 240 V
Load Crest Factor	3 : 1
Topology	Double conversion online
Waveform type	Sine wave
Output Connections	(1) IEC 320 C19 (1) IEC 60320 C19 (6) IEC 60320 C13 (6) IEC 320 C13
Bypass	Internal bypass (automatic and manual)


Input	
Nominal Input Voltage	230V
Input frequency	40 - 70 Hz Auto sensing
Input Connections	IEC 60320 C20
Cord Length	1.5meters
Input voltage range for main operations	110 - 285 Half load, 160 - 280 Full loadV

Disclaimer: Documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user's applications.

Technical Specifications

APC Easy UPS On-Line SRV 3000VA 230V, Argentina. | SRV3KI | Downloaded on 10/03/2022 (EST)

Input	
Number of Power Cords	1
Efficiency at Full Load	88.0 %
Other Input Voltages	220 V, 240 V

Batteries & Runtime	
Battery type	Lead-acid battery
Typical recharge time	4hour(s)
Nominal Battery Voltage	72 V
Replacement Battery	APCRBCV205 
Expected Battery Life (years)	3 - 5
Battery Charge Power (Watts)	60 Watts
Runtime	View Runtime Graph (Available in Technical Tab on site)
Efficiency	View Efficiency Graph (Available in Technical Tab on site)

Communications & Management	
Interface Port(s)	DB-9 RS-232, USB
Control panel	Multifunction LCD status and control console
Audible Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous tone alarm
Available SmartSlot™ Interface Quantity	1

Surge Protection and Filtering	
Surge energy rating	600Joules

Physical	
Maximum Height	336MM, 33.6CM
Maximum Width	190MM, 19.0CM
Maximum Depth	425MM, 42.5CM
Net Weight	26.8KG
Shipping weight	29.0KG
Shipping Height	465MM, 46.5CM
Shipping Width	325MM, 32.5CM

Disclaimer: Documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user's applications.

Technical Specifications

APC Easy UPS On-Line SRV 3000VA 230V, Argentina. | SRV3KI | Downloaded on 10/03/2022 (EST)

Physical	
Shipping Depth	565MM, 56.5CM
Color	Black

Environmental	
Operating Temperature	0 - 40 °C
Operating Relative Humidity	0 - 95 (Non-condensing) %
Operating Elevation	0 - 3000meters
Storage Temperature	-20 - 50 °C
Storage Relative Humidity	0 - 95 (Non-condensing) %
Storage Elevation	0 - 15000meters
Audible noise at 1 meter from surface of unit	50.0dBA
Online thermal dissipation	910.0BTU/hr
Protection Class	IP20

Conformance	
Approvals	CE, EAC, EN/IEC 62040-1, EN/IEC 62040-2, TISI
Standard warranty	2 years repair or replace

Sustainable Offer Status	
RoHS	Compliant

Disclaimer: Documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user's applications.