

## Technical Specifications

APC NetShelter Rack PDU Advanced, Metered, 3Phase, 22.1kW 400V 32A or 17.3kW 415V 30A, 48 Outlets, IEC309 | APDU10350ME |  
Downloaded on 10/18/2023 (EST)



# APC NetShelter Rack PDU Advanced, Metered, 3Phase, 22.1kW 400V 32A or 17.3kW 415V 30A, 48 Outlets, IEC309

APDU10350ME

Call for More Information +358 104466441

Output	
Nominal Output Voltage	240V
Overload Protection	Yes
Maximum Total Current Draw	24
Output Connections	(24) C13/C15 (24) C13/C15/C19/C21

Input	
Nominal Input Voltage	400V 3PH, 415V 3PH
Input frequency	50/60 Hz
Input Connections	IEC 60309 30 A 3P + N + PE
Cord Length	1.8meters
Acceptable Input Voltage	200 - 240, 346 - 415VAC
Load Capacity	17300VA
Maximum Input Current	30A
Regulatory Derated Input Current (North America)	24A

Physical	
Maximum Height	1780MM, 178.0CM
Maximum Width	56MM, 5.6CM
Maximum Depth	75MM, 7.5CM
Net Weight	8.4KG
Shipping weight	11.4KG

**Disclaimer:** Documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user's applications.

## Technical Specifications

APC NetShelter Rack PDU Advanced, Metered, 3Phase, 22.1kW 400V 32A or 17.3kW 415V 30A, 48 Outlets, IEC309 | APDU10350ME |  
Downloaded on 10/18/2023 (EST)



Physical	
Shipping Height	1980MM, 198.0CM
Shipping Width	132MM, 13.2CM
Shipping Depth	262MM, 26.2CM
Color	Black

Environmental	
Operating Temperature	-5 - 60 °C
Operating Relative Humidity	5 - 95 %
Operating Elevation	0 - 3048meters
Storage Temperature	-25 - 65 °C
Storage Relative Humidity	5 - 95 %
Storage Elevation	0 - 15240meters

Conformance	
Approvals	CE, CSA C22.2 No 62368-1, EN 62368-1, FCC part 15 Subpart B, TAA compliance , UL 62368-1
Standard warranty	3 years repair or replace

Sustainable Offer Status	
RoHS	Compliant

**Disclaimer:** Documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user's applications.