

Product data sheet

Specifications



APC NetShelter 6U Wallmount Rack Enclosure Cabinet, Single Hinged, Switch Depth, Unassembled

AR106

Overview

Presentation

Ideal for retail, healthcare, and educational facilities, the wall rack offers an efficient solution for deploying server and networking equipment for edge computing applications. For areas with limited floor space. Designed to house your server, as well as network solutions such as network switches and patch panels. Rack is packaged unassembled for smaller storage and delivery and takes up to 60% less space than assembled alternatives. The door is reversible allowing for the door to open direction desired to avoid interference with its surroundings. Optional 120V fan tray top/bottom mounted. Top/bottom feature knockouts 1/2U of mounting space for accessories. Several APC Smart-UPS models low-profile provide easy UPS integration and mounting. 6U Wall mount cabinet, 8.9 to 12.9 inches mounting depth, 200lb weight capacity, 19" rack width, ships unassembled, 5 year APC warranty.

Lead time

Usually in Stock

Main

Product or Component Type

Rack enclosure

Number of rack unit

6U

Physical

Height

14.02 in (35.6 cm)

Width

23.58 in (59.9 cm)

Depth

15.75 in (40 cm)

Net Weight

20.70 lb(US) (9.39 kg)

Color

Black

Mounting Support

Wall

Mounting preference

No preference

Mounting Mode

Not rack-mountable

Maximum Mounting Depth

12.95 in (32.89 cm)

Minimum Mounting Depth

8.90 in (22.61 cm)

Rack Width

19"

Permanent permissible load

200 lb(US) (90.72 kg) static

Conformance

Standards

EIA-310E

Ordering and shipping details

GTIN

731304317265

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11.54 in (29.3 cm)
Package 1 Width	19.09 in (48.5 cm)
Package 1 Length	27.09 in (68.8 cm)
Package 1 Weight	32.10 lb(US) (14.56 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
Take-back	Take-back program available

Contractual warranty

Warranty	5 year repair or replace
----------	--------------------------

Recommended replacement(s)