

Product data sheet

Specifications



APC NetShelter 12U Wallmount Rack Enclosure Cabinet Single Hinged Server Depth

AR112SH6

Overview

Presentation

Ideal for retail, healthcare, and educational facilities, this wall mount rack offers an efficient solution for deploying server and networking equipment for edge computing applications. This rack enclosure is wall mountable, ideal for areas with limited floor space, and is designed specifically for servers and network switches and patch panels. The cabinet's door is reversible and is compatible with APC's Netbotx security upgrade to provide remote access, video surveillance, and environmental monitoring (sold separately). Optional 120V fan tray can be top or bottom mounted (sold separately) Both the top and bottom feature knockouts of 1/2U mounting space for accessories. And several APC Smart-UPS models low-profile provide easy UPS integration and mounting 12U Wall mount cabinet, mounting depth range of 2.87 to 20.8 inches, 200lb weight capacity, 19" rack width, ships fully assembled, ventilated with accessory integration options, 5 year APC warranty.

Lead time Usually in Stock

Main

Product or Component Type Rack enclosure

Number of rack unit 12U

Physical

Height 24.41 in (62 cm)

Width 23.62 in (60 cm)

Depth 23.62 in (60 cm)

Net Weight 42.31 lb(US) (19.19 kg)

Color Black

Mounting Support Wall

Mounting preference No preference

Mounting Mode Not rack-mountable

Maximum Mounting Depth 20.80 in (52.83 cm)

Minimum Mounting Depth 2.87 in (7.29 cm)

Rack Width 19"

Permanent permissible load 200 lb(US) (90.72 kg) static

Conformance

Standards UL 2416
EIA-310E

Ordering and shipping details

GTIN 731304402725

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	27.56 in (70 cm)
Package 1 Width	26.97 in (68.5 cm)
Package 1 Length	26.97 in (68.5 cm)
Package 1 Weight	51.10 lb(US) (23.18 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	5 year repair or replace
----------	--------------------------

Recommended replacement(s)