

# Product data sheet

Specifications



## NetShelter 2 Post Rack 45U #12-24 Threaded Holes Black

AR201

### Overview

Lead time Usually in Stock

### Main

Number of rack unit 45U  
Number of cables 1  
Provided equipment 24 x #12-24 x 0.5 inch pilot screws  
User Manual

### Physical

Color Black  
Height 84.09 in (213.6 cm)  
Width 20.20 in (51.3 cm)  
Depth 14.80 in (37.6 cm)  
Net Weight 26.06 lb(US) (11.82 kg)  
Mounting Location Front  
Mounting preference No preference  
Mounting Mode Not rack-mountable  
Maximum Mounting Depth 41.26 in (104.8 cm)  
Rack Width 19"  
Marking 3 gauge post  
Permanent permissible load 750 lb(US) (340.19 kg) static

### Conformance

Product Certifications UL Listed  
TAA  
Standards EIA-310E

### Ordering and shipping details

GTIN 731304015574

### Packing Units

Unit Type of Package 1 PCE

<b>Number of Units in Package 1</b>	1
<b>Package 1 Height</b>	3.94 in (10 cm)
<b>Package 1 Width</b>	86.61 in (220 cm)
<b>Package 1 Length</b>	6.30 in (16 cm)
<b>Package 1 Weight</b>	30.86 lb(US) (14 kg)

## Offer Sustainability

<b>Sustainable offer status</b>	Green Premium product
<b>REACH Regulation</b>	<a href="#">REACH Declaration</a>
<b>REACH free of SVHC</b>	Yes
<b>EU RoHS Directive</b>	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
<b>Toxic heavy metal free</b>	Yes
<b>Mercury free</b>	Yes
<b>RoHS exemption information</b>	<a href="#">Yes</a>
<b>Take-back</b>	Take-back program available

## Contractual warranty

<b>Warranty</b>	2 years repair or replace
-----------------	---------------------------

## Recommended replacement(s)